



MICR Cheque Qualifier

RDM's Quality Control Solution

QUALITY CONTROL.
REJECT REDUCTION.
USER-FRIENDLY.



Product Overview

RDM's MICR Qualifier GTX is the next generation in MICR (Magnetic Ink Character Recognition) Quality Control Workstations. Developed in response to the needs of bank item processing centers and document printers, the GTX delivers user-friendly features such as a graphical display of MICR characters, analysis of character dimensions, and embedded PDF reporting.

The GTX demystifies the process of identifying reject causes. It facilitates communication between banks, corporations and printers, improving MICR quality and reducing costly rejects.

As a component of RDM's "Reject Reduction" solution, the MICR Qualifier GTX is an invaluable tool for banks, payment processing centers, corporate clients and check printers. With the advent of laser MICR printing, a change from signal strength problems to MICR character dimensional quality problems has occurred. Using the highest level of detection technology, we test beyond the American Bankers Association (ABA) and American National Standards Institute (ANSI) X9.27 and X9.13 standards.

Analysis Tool - Powerful Reporting-

When utilizing the GTX reporting software, banks have, on average, resolved 35% or more of their MICR related problems within 60 days. The speed and efficiency of the GTX allows the preparation for more reports in a shorter period of time.

Scientific Instrument -Cutting Edge Technology

The Qualifier GTX utilizes high-speed, straight-through transports that have reader/sorter grade components with technology that can analyze a document in seconds. The GTX identifies all common problems including; signal level, line format, spacing, MICR line intrusions, extraneous ink, character dimensions and font issues.

Individual character representation and user programmable signal alarm levels ensure the highest level of quality analysis.

The GTX supports multiple international formats and newer digital print technologies such as laser. Ease of use is ensured through user-friendly software and single click operations.

Key Features

- ▶▶ Report Generation
- ▶▶ Graphical representation of ANSI character dimensions
- ▶▶ PDF file formats of analysis screens
- ▶▶ Save data to disk
- ▶▶ Embedded PDF reporting
- ▶▶ Dimensional waveform analysis
- ▶▶ Character spacing data table
- ▶▶ Extraneous ink detection
- ▶▶ French language format available

User-Friendly Software

The MICR Qualifier GTX clearly explains where and how MICR Characters deviate from allowable tolerances. Older equipment produces difficult to read "waveform" reports that require significant technical expertise to understand. With the GTX's advanced reporting functions, it is easy for even non-technical people to clearly explain print quality issues.

PDF analysis file easily generated and email to any PC with Adobe™

Product Specifications

100 inch/second transport speed

ANSI specified read/write head and amplifier

Test entire 5/8" clear-band

Power Supply: 115 VAC, 60 Hz; 220, 240 VAC 50 Hz

Weight: 27 lb.

Dimensions: 13"(W) x 8"(H) x 10"(L)

Minimum PC Requirements

Pentium IV, 200 MB available hard disk space

Windows 2000/XP/Vista

1024 x 796 video set to 256 colors

Windows supported printer

Summary of the analysis

Dimensions that are out of ANSI spec are highlighted and detailed

Dimension	Ideal	Actual	Actual allowed	In Specification	Out of specification
A	37	35	34 to 40	Yes	
B	14	15	11 to 17	No	■
C	12	12	9 to 15	Yes	
D	64	65	61 to 67	Yes	
E	125	124	115 to 135	Yes	
F	125	125	115 to 135	Yes	

Tables show the critical font dimensions that are at fault, and what the nominal ANSI dimensions and tolerances are.

Copyright © 2011, RDM Corporation. All right reserved. RDM and the RDM logo are trademarks of RDM Corporation. RDM Corporation reserves the right to make changes to its specifications of all its products without notice.

July 2011

Business Smart Solutions Pty. Ltd.

Committed to Excellence

www.bss.com.au
info@bss.com.au

All products, images and brand names are trademarks and are owned by the respective holders and are used for descriptive purposes only. They are neither affiliated with, endorse, or sponsor the use of this product. All specifications are subject to change for improvement purposes without prior notice.